

**NEW  
Materials  
Available**

Rubber Fab Technologies Group's

# GAUGE PROTECTION SYSTEM

Assures Protection of  
Instrumentation with  
No Product Loss



**Available  
Materials Include:**

- Platinum Silicone
- PTFE **NEW!**
- Tuf-Steel **NEW!**
- FKM
- EPDM

The Rubber Fab Gauge Guard Isolator seals **protect expensive stainless steel diaphragms and instruments from damage without affecting instrument performance**. By combining a quality Rubber Fab hygienic seal with a membrane, the Gauge Guard Isolator hygienic seal **isolates corrosive solutions from the stainless steel diaphragm**. A necessary and **cost effective** step in **assuring long life and accurate results from your gauges**.

As some manufacturers will suggest the use of a gauge guard seal, others note that the **failure to use a gauge guard seal can void most instrument and gauge warranties**.

**All the Rubber Fab Benefits in a Gauge Guard Hygienic Seal**

- Seal membrane **protects stainless steel diaphragm from corrosive solutions**
- **Will not interfere with gauge operation or accuracy**
- Works with most industry standard instruments
- Helps **extend the life** of gauges
- Available in:  
**Platinum Silicone**  
**PTFE**  
**Tuf-Steel®**  
**EPDM**  
**FKM Fluoroelastomer**
- 1/2" and 3/4" – .015 membrane thickness
- 1", 1-1/2" and 2" – .010 membrane thickness

**All Rubber Fab Hygienic Seals Meet the Stringent Standards For Purity**

- U.S. Pharmacopeia Class VI Certification
- Cytotoxicity Criteria
- Title 21 CFR 177.2600
- USDA and 3-A Sanitary Standards
- Current Good Manufacturing Practices (CGMP)
- ASME-BPE Standards
- Animal Derived Ingredient Free

© ADI Free is a registered trademark of Rubber Fab Technologies Group



26 Brookfield Drive • Sparta, NJ 07871  
 973.579.2959 • Toll Free: 866.442.2959  
 Fax: 973.579.7275 • sales@rubberfab.com

[www.rubberfab.com](http://www.rubberfab.com)



**EPDM**

|        |             |
|--------|-------------|
| 1/2"   | 42GGI-E-050 |
| 3/4"   | 42GGI-E-075 |
| 1"     | 40GGI-E-100 |
| 1-1/2" | 40GGI-E-150 |
| 2"     | 40GGI-E-200 |

**Temperature: Up to 250°F**



**Platinum Silicone**

|        |              |
|--------|--------------|
| 1/2"   | 42GGI-PX-050 |
| 3/4"   | 42GGI-PX-075 |
| 1"     | 40GGI-PX-100 |
| 1-1/2" | 40GGI-PX-150 |
| 2"     | 40GGI-PX-200 |

**Temperature: Up to 300°F**



**FKM Fluoroelastomer**

|        |               |
|--------|---------------|
| 1/2"   | 42GGI-SFY-050 |
| 3/4"   | 42GGI-SFY-075 |
| 1"     | 40GGI-SFY-100 |
| 1-1/2" | 40GGI-SFY-150 |
| 2"     | 40GGI-SFY-200 |

**Temperature: Up to 400°F**



**PTFE**

|        |             |
|--------|-------------|
| 1"     | 40GGI-G-100 |
| 1-1/2" | 40GGI-G-150 |
| 2"     | 40GGI-G-200 |

**Temperature: Up to 450°F**



**Tuf-Steel®**

|        |              |
|--------|--------------|
| 1"     | 40GGI-TS-100 |
| 1-1/2" | 40GGI-TS-150 |
| 2"     | 40GGI-TS-200 |

**Temperature: Up to 500°F**

Rubber Fab Technologies Group is a member of:

Distributed by:



Email [info@puretransfer.com](mailto:info@puretransfer.com)  
[www.puretransfer.com](http://www.puretransfer.com)  
 Tel: 033 39 390 034